



## PBSS9

by Wiegmann  
Catalog ID: PBSS9

N4X 30.5 MM 9 Pushbutton Enclosure 9.5X8.5X3 304 Stainless Steel

- Bodies and doors fabricated from 14 gauge 304 stainless steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Enclosures have internal detachable hinges to hold cover open during wiring, yet permit quick removal. Grounding provisions provided.

## Product Details

### General

Application	Designed to hold all standard brands of pushbuttons, switches, and pilot lights. Provide protection from dust, dirt, oil, and water. PBSS Series designed for areas where serious corrosion problems exist.
Construction	Continuously Welded Seams
Cover Type	Pushbutton
Knockouts	No
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Holes	9
Pushbutton Number of Holes	9
Pushbutton Size	30.5 MM
Series	PBSS
Type	Enclosure
UPC	786725433308

### Dimensions

Actual Depth	3.09 in
Actual Height	9.500 in
Actual Width	8.500 in

Depth	3 in
Height	10 in
Weight	7 lb
Width	9 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	4X
UL Listed	Yes