



PBXD10

by Wiegmann
Catalog ID: PBXD10

N4 30.5 MM 10 Deep Pushbutton Enclosure 14X6.2X4.7 Carbon Steel - Gray

- Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Enclosures have internal detachable hinges to hold cover open during wiring, yet permit quick removal. Grounding provisions provided.

Product Details

General

| | |
|-----------------|---|
| Application | Designed to hold 30.5mm oil-tight pushbuttons, switches, and pilot lights. Provide protection against dirt, dust, oil, and water. Extra deep design accommodates additional contact blocks for pushbuttons. |
| Color | Gray |
| Construction | Continuously Welded Seams |
| Cover Type | Pushbutton;Screw |
| Finish Type | Polyester Powder |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | External Mounting Plates |
| Mounting Type | Wall Mount |
| Number of Holes | 10 |
| Series | PBXD |
| Type | Deep Pushbutton Enclosure |
| UPC | 786725431427 |

Dimensions

| | |
|--------------|----------|
| Actual Width | 6.250 in |
| Depth | 14 in |
| Height | 14 in |
| Weight | 8 lb |

| | |
|-------|------|
| Width | 6 in |
|-------|------|

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | 4 |
| UL Listed | Yes |