



PBYX42

by Wiegmann
 Catalog ID: PBYX42

N12 30.5 MM 42 Pushbutton Continuous Hinge Enclosure 21X17.5X6 Carbon Steel - Gray

Designed to hold 30.5mm oil-tight pushbuttons, switches, and pilot lights with extra size to allow 2.50" between centers of pushbutton holes. Provide protection against dirt, dust, oil, and water.

- Fabricated from 14 gauge steel. Continuously welded seams ground smooth. Cover held in place by continuous hinge. Back panel included with enclosure. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Grounding provisions provided.

Product Details

General

Application	Designed to hold 30.5mm oil-tight pushbuttons, switches, and pilot lights with extra size to allow 2.50" between centers of pushbutton holes. Provide protection against dirt, dust, oil, and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Pushbutton;Screw
Finish Type	Polyester Powder
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Number of Holes	42
Series	PBXY
Type	Wide Center Space Pushbutton Enclosure
UPC	786725432806

Dimensions

Actual Width	17.5 in
Depth	6 in
Height	21 in

Weight	37 lb
Width	18 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL • CSA
Nema Rating	NEMA 12
UL Listed	Yes