



PBYX4S

by Wiegmann
 Catalog ID: PBYX4S

N12 30.5 MM 4 Pushbutton Continuous Hingle Enclosure 8.5X7.5X6 Carbon Steel - Gray

Designed to hold 30.5mm oil-tight pushbuttons, switches, and pilot lights with extra size to allow 2.50" between centers of pushbutton holes. Provide protection against dirt, dust, oil, and water.

- Fabricated from 14 gauge steel. Continuously welded seams ground smooth. Cover held in place by continuous hinge. Back panel included with enclosure. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Grounding provisions provided.

Product Details

General

| | |
|-----------------|--|
| Application | Designed to hold 30.5mm oil-tight pushbuttons, switches, and pilot lights with extra size to allow 2.50" between centers of pushbutton holes. Provide protection against dirt, dust, oil, and water. |
| Color | Gray |
| Construction | Continuously Welded Seams |
| Cover Type | Pushbutton;Screw |
| Finish Type | Polyester Powder |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | External Mounting Plates |
| Mounting Type | Wall Mount |
| Number of Holes | 4 |
| Series | PBXY |
| Type | Wide Center Space Pushbutton Enclosure |
| UPC | 786725432387 |

Dimensions

| | |
|---------------|----------|
| Actual Height | 8.500 in |
| Actual Width | 7.500 in |
| Depth | 6 in |

| | |
|--------|------|
| Height | 9 in |
| Weight | 8 lb |
| Width | 8 in |

Certifications and Compliance

| | |
|------------------|---|
| Certified Listed | <ul style="list-style-type: none"> • UL • CSA |
| Nema Rating | NEMA 12 |
| UL Listed | Yes |