



PF-300

by CMC
Catalog ID: PF-300

Above-grade pedestal with covered connectors, Pedestal, Base & Cover- Linear low-density polyethylene, Connector Body - Extruded 6061-T6 aluminum, Connector Cover - Clear, co-polyester, Covers: Made of clear, hard lexan

- Standard Mussel green tint and ultraviolet stabilizer ensure an attractive and long- lasting pedestal. Add suffix "LG" for light willow green tint
- Pedestal ribbing ensures in-ground stability where driven stakes are not used
- Stainless steel penta-head lock assembly
- Linear low-density polyethylene rotational molding process produces superior fit and finish, with high impact and tensile strength and a dielectric strength of 450 volts/mil
- Incorporates unique molded connector brackets that support the mounted connectors
- Clear, hard Lexan cover
- clear or black plastisol cover available
- Connector set-screws accept a 5/16" Allen wrench. Recommend 9" insulated Allen wrench

Product Details

General

Material	Aluminum Alloy, 6061-T6
UPC	192663119585

Dimensions

Depth	33 in
Height	38.375 in
Length	24.125 in
Width	12.125 in

Conductor Related

Conductor Range

Pedestal Only



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

