

Wire Basket Tray Tray Section Overhead Tray, 118" Length

HUBBELL

Features

- For use in control environments
- Top rail T-weld construction prevent snags
- 5mm round wire minimum



Ordering Information

Height	Width	Catalog Number	UPC Number
2"	12"	HBT0212BK	783585416298

Standards

UL/cUL Classified as equipment grounding conductor
ASTM A 641

Specifications

Material	100% Recycled Steel
Color	Black
Flat Shaped Cross-Wires	Cable Support Area- .03125 square inch
Paint	Polyester TGIC Powder Coating
Ground Point	Masked for bonding
Mesh Spacing	2" x 4" (50.5 x 101.6)

Performance

No-Splice Support Spacing	5' (1524)
Splice Kit Qty- 90 Degree Sweep Elbow	6
Splice Kit Qty- Straight Splice	4
Support Spacing	6' (1828.8)
Tray Area (cu. in.)	24
Weight Capacity (lb/ft)	58

Dimensions- inches (mm)

Height	2" (51)
Width	12" (305)
Length	118" (2997.2)

Accessories

Angled Cutting Tool	HBTCUTTOOL
Splice Kit	HBTSKBK
Corner Splice	HBTCGBK
Black Steel Cover	HBTCVR12BK
Black Steel Divider	HBTDIV2BK

Online Resources

eCatalog

