

Patch Cord

Features

- Third Party Verified Category 6A Component
- Plug Optimized For High Density Switch Ports
- 10-Gigabit Application Assurance
- Qualified to 150% of 802.3bt PoE Current Level



Ordering Information

Description	Color	Catalog Number	UPC
15 ft. Category 6 Patch Cord	Gray	HCL6AGY15	

Listings

ANSI/TIA/EIA-568-C.2 Category 6 component
UL Listed 1863

Specifications

Conductor	28AWG F/UTP
Jacket	Flame-Retardant PVC-CMR Rated
Plug Body	Polycarbonate UL 94V-0
Plug Boot	Polycarbonate UL 94V-0
Contact Plating	50 micro-inch Gold with 100 micro-inch under plating
OD	0.186 in.

Performance

Mechanical

Cable to plug tensile strength	20+ lbs.
Mating Cycles	2000+

Applications

IEEE 802.3an 10GBASE-T
IEEE 802.3bt 4PPoE Power over Ethernet

Accessories

Category 6A Component Jack	HXJ6AGY
Category 6A 24-Port Patch Panel	HP6A24
Category 6A 48-Port Patch Panel	HP6A48

Online Resources

[eCatalog](#)