

HFCD1 Series Hubbell Brand Indoor Tight Buffer Distribution

HUBBELL

Features

- Corning ULTRA SMF-28® Singlemode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Ordering Information

Catalog No.	UPC
HFCB1006PS	662620340692

Listings

ANSI/ICEA S-83-596
NFPA-262/UL910/CSA FT-6
Telcordia GR-409
TIA-568.3-D

Specifications

Number of Fibers	6
Cable Rating	Plenum
Fiber Type	OS2, SM
Color	Yellow

Characteristics

Application	Data Transmission
Attenuation	0.5/0.4 Db per Kilometer
Material - Jacket	PVC
Temperature Rating	0 Degrees °C to 70 Degrees °C
Wavelength	1310/1550 Nanometers

