

# OptiChannel Indoor/Outdoor Tight Buffer Cable Plenum


# HUBBELL

## Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

## Ordering Information

Description	Fiber	Catalog Number	UPC Number
72 strand, OM4, MM, I/O Tight Buffer Plenum, Indoor/Outdoor Tight Buffer - Black	OM4 Multimode	HFCD14072P4BK	662620555744



## Listings

ANSI/ICEA S-83-596  
TIA-568.3-D  
NFPA-262/UL910/CSA FT-6  
Telcordia GR-409 and GR-20

## Specifications

Fiber Coating	900 Micron PVC Tight Buffer
Cable Diameter in (mm)	0.79 (20)
Cable Weight (lb/kft)	238
Construction	Multi-Unit, 12F/Unit, Central Strength Member
Armor	None

## Performance

### Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

### Maximum Installation Pulling Load (lb)

600

### Maximum Operating Temperature

-4°F to +185°F (-20°C to +85°C)

### Minimum Bend Radius, In-Service in (cm)

7.9 (20)

## Accessories

Fiber Strip Tool	OFSTRIP2
Splice Tray, 12 Fusion	STRAY12F
Splice Tray, 24 Fusion	STRAY24F
Splice Protection Sleeves	FSHST401025

## Online Resources

eCatalog