

Grounding & Bonding Compression Lugs Single Pack

HUBBELL

Features

- Long barrel compression lugs are the best solution for building a low-resistant bond
- HPW lugs are die index traceable when using a properly sized die for compression
- Lugs are tin plated and have an inspection window to ensure that the conductor is fully listed



Ordering Information

Description	Mounting Hole Size	UPC Number	Catalog Number
Compression Lugs, #2 AWG Double Hole, 1 Pack	ID: 0.375", Spaced: 1"	662620619316	HGBL02DB1

Listings

c-UL-us Listed
TIA-607 Compliant

Specifications


Material	Tin-Plated Copper
Barrel Color	Brown
Die Index #	10
Bend Angle	Straight
Lug Mount Style	DB

Accessories

Manual Crimp Tool	HMD7
X-Die for Manual Tool	HX2CRT
12 Ton Power Crimp Tool	HPAT750LI
U-Die for Power Tool	HU2CRT

Resources

Customer Use Drawing
Grounding & Bonding Brochure



Dimensions in. (mm)

A	3.4" (86)
B	0.7" (18)
C	0.4" (10)
D	1" (25)

