

Grounding & Bonding Compression Lugs Single Pack

HUBBELL

Features

- Long barrel compression lugs are the best solution for building a low-resistant bond
- HPW lugs are die index traceable when using a properly sized die for compression
- Lugs are tin plated and have an inspection window to ensure that the conductor is fully listed



Ordering Information

Description	Mounting Hole Size	UPC Number	Catalog Number
Compression Lugs, #4 AWG Double Hole, 1 Pack	ID: 0.25", Spaced: 0.625 in	662620618968	HGBL04D1

Listings

c-UL-us Listed
TIA-607 Compliant

Specifications


Material	Tin-Plated Copper
Barrel Color	Gray
Die Index #	8
Bend Angle	Straight
Lug Mount Style	D

Accessories

Manual Crimp Tool	HMD7
X-Die for Manual Tool	HX4CRT
12 Ton Power Crimp Tool	HPAT750LI
U-Die for Power Tool	HU4CRT

Resources

Customer Use Drawing
Grounding & Bonding Brochure



Dimensions in. (mm)

A	2.7" (69)
B	0.5" (13)
C	0.3" (8)
D	0.63" (16)

