

# Grounding & Bonding Compression Lugs Single Pack

# HUBBELL

## Features

- Long barrel compression lugs are the best solution for building a low-resistant bond
- HPW lugs are die index traceable when using a properly sized die for compression
- Lugs are tin plated and have an inspection window to ensure that the conductor is fully listed

## Ordering Information

Description	Mounting Hole Size	UPC Number	Catalog Number
Compression Lugs, #6 AWG Double Hole, 1 Pack	ID: 0.25", Spaced: 0.625 in.	662620619385	HGBL06DF1

## Listings

c-UL-us Listed  
TIA-607 Compliant

## Specifications


Material	Tin-Plated Copper
Barrel Color	Blue
Die Index #	7
Bend Angle	45 Degrees
Lug Mount Style	D

## Accessories

Manual Crimp Tool	HMD7
X-Die for Manual Tool	HX5CRT
12 Ton Power Crimp Tool	HPAT750LI
U-Die for Power Tool	HU5CRT

## Resources

Customer Use Drawing  
Grounding & Bonding Brochure



### Dimensions in. (mm)

A	2.5" (62)
B	0.5" (13)
C	0.3" (8)
D	0.63" (16)