

# Grounding & Bonding Compression Lugs Single Pack

# HUBBELL

## Features

- Long barrel compression lugs are the best solution for building a low-resistant bond
- HPW lugs are die index traceable when using a properly sized die for compression
- Lugs are tin plated and have an inspection window to ensure that the conductor is fully listed

## Ordering Information

Description	Mounting Hole Size	UPC Number	Catalog Number
Compression Lugs, #6 AWG Double Hole, 1 Pack	ID: 0.25", Spaced: 0 in.	662620619378	HGBL06SF1

## Listings

c-UL-us Listed  
TIA-607 Compliant

## Specifications

Material	Tin-Plated Copper
Barrel Color	Blue
Die Index #	7
Bend Angle	45 Degrees
Lug Mount Style	S


## Accessories

Manual Crimp Tool	HMD7
X-Die for Manual Tool	HX5CRT
12 Ton Power Crimp Tool	HPAT750LI
U-Die for Power Tool	HU5CRT

## Resources

Customer Use Drawing  
Grounding & Bonding Brochure

Need Pic



## Dimensions in. (mm)

A	2" (51)
B	0.5" (13)
C	0.3" (8)