

OptiChannel
Simplex Fiber Patch Cords, Riser
LC to LC, Singlemode, OS2

HUBBELL

Features

- Precision Zirconia Ferrule, UPC Polish
- 100% Tested, Heat Cured Epoxy Termination
- Available in Lengths 1 to 5, 10 meters
- Custom Lengths Quoted to Order

Ordering Information

Description	Cable Type	Catalog Number	UPC
Fiber Patch Cord, Riser, Simplex, LC to LC, OS2, 2M	Simplex Jacket, Yellow	SFRCLCLCS2SM	662620613857

Standards

TIA-568.3
 TIA-604-FOCIS
 Telcordia GR-326-CORE
 TIA-492CAAB (OS2, Bend Tolerant)
 ANSI/ICEA S-83-596
 TIA-598

Specifications

Overall Length	2 meters (6.56 ft)
Ferrule Material	Zirconia Ceramic
Cable Diameter	1.6 mm to 2.0 mm
Mated Pair Insertion Loss	< 0.35 dB (0.15 dB Typical)
Mated Pair Return Loss	> 55 dB
Polarity	A

Performance

Mechanical	
Mating Durability	500 Cycles, < 0.75dB
Minimum Bend Radius	25 mm (1.0 in.)
Operating Temperature Range	0C to 70C (32F to 158F)
Tensile Rating, Short Term	11.24 Lb (50 N)

Applications


10 Gbps/25 Gbps Fiber Channel
 Backbone/Horizontal Distribution Interconnect
 Data Center Equipment Interconnect

Accessories

Fiber Microscope, 200X	OFSCOPE2
Fiber Cleaning Kit	OFCLEANKT1
Fiber Wipes Dispenser, 90 Sheets	OFWIPES90
Fiber Cleaning Fluid, 3 Oz.	OFCLEANER3OZ

Online Resources

eCatalog



CABLE TYPE	CABLE COLOR	POLISH(A)	CONN. COLOR (A)	BOOT COLOR (A)	POLISH (B)	CONN. COLOR (B)	BOOT COLOR (B)
9/125 OS2	YELLOW	UPC	BLUE	WHITE	UPC	BLUE	WHITE

