

FSP Adapter Panel, Jack, 6-Port, Unloaded

By Hubbell Premise Wiring
Catalog # [FSPNHD6X](#)

FSP Adapter Panel, Jack, 6-Port, Unloaded



Features

- Wide Range of Adapter Types
- Quick and Easy Snap-in Design
- Premium Quality and High Performance

Application

Interconnect

Specifications

Industry Standard(s)	• TIA-568-C.3
	• TIA-604-FOCIS

Conductor

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Configuration

Number Of Ports	6
-----------------	---

Current

Insertion Loss	0.30 dB
Return Loss	26

General

Color	Black
UPC	662620671697
Material - Mounting Hardware	Snap-In
Sub Brand	OptiChannel
Material	Ceramic Zirconium

Logistics

Carton Quantity	4
-----------------	---

Operational

Repeatability	0.1 dB
Service Life	500 matings
Adapter Type	JACK_PACK, Unloaded
Temperature Rating	-40C to +85C

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)