


HUBBELL

Premise Wiring

Fiber Optic Panel Adapter, 24-Fiber, 12 LC Duplex, Zircon Sleeves, Yellow

By Hubbell Premise Wiring
Catalog # [FSPNLCDS12Y](#)

Fiber Optic Panel Adapter, 24-Fiber, 12) LC Duplex, Zircon Sleeves, Yellow



Features

- Premium Quality and High Performance Design

Application

Interconnect

Specifications

- | | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">TIA-568-C.3TIA-604-FOCIS |
|----------------------|---|

Conductor

- | | |
|------------|-------------------------|
| Fiber Size | 125 Micron |
| Fiber Type | Singlemode or Multimode |

Configuration

- | | |
|-----------------|----|
| Number Of Ports | 12 |
|-----------------|----|

Current

- | | |
|----------------|---------|
| Insertion Loss | 0.30 dB |
| Return Loss | 26 |

Dimensions

- | | |
|------|-------------|
| Size | 5.1" X 1.1" |
|------|-------------|

General

- | | |
|------------------------------|-------------------|
| Color | Yellow |
| UPC | 662620671789 |
| Material - Mounting Hardware | Snap-In |
| Sub Brand | OptiChannel |
| Material | Ceramic Zirconium |

Logistics

- | | |
|-----------------|---|
| Carton Quantity | 4 |
|-----------------|---|

Operational

- | | |
|--------------------|-----------------------|
| Repeatability | 0.1 dB SM / 0.2 dB MM |
| Service Life | 500 matings |
| Single/Multimode | SM/MM |
| Adapter Type | LC Duplex |
| Temperature Rating | -40C to +85C |

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)