


Fiber Optic Panel Adapter, 24-Fiber, 6 LC Quad, Phosphor Zircon Sleeves, Orange

By Hubbell Premise Wiring

Catalog # [FSPNLCQS6OR](#)

Fiber Optic Panel Adapter, 24-Fiber, 6) LC Quad, Phosphor Bronze Sleeves, Orange



Features

- Premium Quality and High Performance Design

Application

Interconnect

Specifications

Industry Standard(s)	- TIA-568-C.3 - TIA-604-FOCIS
----------------------	---

Conductor

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Configuration

Number Of Ports	24
-----------------	----

Current

Insertion Loss	0.30 dB
Return Loss	55

General

Color	Orange
UPC	662620340104
Material - Mounting Hardware	Snap-In
Sub Brand	OptiChannel
Material	Ceramic Zirconium

Logistics

Carton Quantity	4
-----------------	---

Operational

Repeatability	0.2 dB
Service Life	500 matings
Single/Multimode	SM/MM
Adapter Type	LC Quad
Temperature Rating	-40C to +85C

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)