


Fiber Optic Panel Adapter, 4 Adapter
Openings, Unloaded

By Hubbell Premise Wiring
Catalog # [FSPNSCD4X](#)

Fiber Adapter Panel, 4 Adapter Openings, Unloaded



Features

- Premium Quality and High Performance Design

Application

Interconnect

Specifications

Industry Standard(s)	• TIA-568-C.3 • TIA-604-FOCIS
Conductor	
Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

Configuration

Number Of Ports	4
-----------------	---

Current

Insertion Loss	0.30 dB
----------------	---------

Dimensions

Size	5.1" X 1.1"
------	-------------

General

UPC	662620340234
Material - Mounting Hardware	Snap-In
Sub Brand	OptiChannel
Material	Ceramic Zirconium

Logistics

Carton Quantity	4
-----------------	---

Operational

Service Life	500 matings
Adapter Type	SC Duplex Openings
Temperature Rating	-40C to +85C

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)