

Fiber Optic Panel Adapter, 12-Fiber, 6) SC
Duplex, Phosphor Bronze Sleeves, Red

By Hubbell Premise Wiring
Catalog # [FSPSCDM6R](#)

Fiber Optic Panel Adapter, 12-Fiber, 6-SC Duplex Sleeves



Features

- Premium Quality and High Performance Design

Application

Interconnect

Specifications

EU RoHS Indicator	Yes
Industry Standard(s)	<ul style="list-style-type: none">TIA-568-C.3TIA-604-FOCIS

Conductor

Fiber Size	125 Micron
Fiber Type	Multimode

Configuration

Number Of Ports	12
-----------------	----

Current

Insertion Loss	0.30 dB
Return Loss	26
Connectivity	Receptacle

General

Color	Red
UPC	662620212029
Material - Mounting Hardware	Snap-In
Material	Phosphor Bronze

Logistics

Carton Quantity	4
-----------------	---

Operational

Repeatability	0.2 dB
Adapter Type	SC Duplex
Temperature Rating	-40C to +85C
Service Life	500 matings
Single/Multimode	MM