

ST19 LED Lamp

Lamp socket Mounted • Damp Location Listed PROGRESS LED



Description:

Accessory bulb to give you options and design versatility when creating your desired lighting experience. Clear glass bulb with medium base. Dimmable to 10%. Features 7w with 2700K color temperature.

Specifications:

- Clear glass
- Filament bulb.
- 7w
- 2700K
- 15,000 hours
- Measures 2-1/2-inch width by 5-1/2-inch height.
- 3-year Limited Warranty
- Fully dimmable.

Performance:

| | |
|------------------------|---|
| Number of Modules | 1 |
| Input Power | 7 W |
| Input Voltage | 120 V |
| Input Frequency | 60 Hz |
| Lumens/LPW (Delivered) | 1,057/52 (LM-79) |
| CCT | 2700 K |
| CRI | 90 CRI |
| Life (hours) | 15000 (L70/TM-21) |
| Min. Start Temp | -30 °C |
| Warranty | 5-year Limited Warranty |
| Labels | cETLus Damp Location Listed ENERGY STAR® qualified Meets California Title 24 JA8-2016 |

F7ST19DLED927/JA8



Dimensions:

Diameter: 2-1/2 in
Height: 5-1/2 in