

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P2100-104

Elina

Three-light bath from the Elina Collection spins a traditional classic and modern form by exaggerating its heirloom quality details. The fixture's tall, trumpeted opal glass, K9 glass orb accents and polished nickel finish create the distinctive silhouette.

- Polished Nickel finish.
- Heirloom quality details.
- Tall, trumpeted opal glass.
- K9 glass orb accents.
- Socket tool included (7-7/8" x 2-5/8" & 2").

Category: Bath & Vanity

Finish: Polished Nickel (plated)

Construction: Steel Construction

Glass/Shade: Etched opal glass shades, Clear K9 orb accents



Width: 23"
Height: 10-1/4"
Depth: 6-1/4"
H/CTR: 4" (glass facing up)

Glass
Width: 4-3/4"
Height: 7-3/16"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Fixture can be installed with glass facing up or down Back plate covers a standard 4" octagonal recessed outlet box 7.5" W., 4.5" ht., 0.875" depth Includes socket ring tool	Pre-wired 6" of wire supplied 120 V	Quantity: Three 100w max. Medium Base E26 base porcelain sockets	UL-CUL Damp location listed 1 year warranty