

Claret

Ceiling Mounted • Dry Location Listed **PROGRESS LED**

Description:

Claret Collection 5-Blade Reversible Matte Black/American Walnut 56-Inch AC Motor

Specifications:

- White Opal Glass Bowl
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6.5 in W., 2.5 in ht., 6.5 in depth
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,400
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	cULus Dry Location Listed Meets California Title 24 JA8-2016 AC motor

P250007-009-30



Dimensions:

Length: 54 in
 Diameter: 54 in
 Height: 15-1/8 in

White Opal Glass Bowl
 Width: 7-1/4 in
 Height: 1-7/8 in

P250007-009-30

Dimming Notes:

P250007-009-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06

IDevices IDEV009

Leviton 6681

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.