

Ceiling downrod mounted • Dry location listed

Description:

Enhance your home with the perfect mix of form and function with the 32" four-blade Drift fan. Ideal for smaller spaces, such as closets, mudrooms and laundry rooms, Drift features a powerful motor and a steep pitch to circulate a lot of air within a smaller space. Drift offers a dual mount system and a three-speed pull chain fan switch, as well as an on/off pull chain switch to operate the light.

Specifications:

- Architectural Bronze (-129) (painted)
- Steel construction
- Enhance your home with the perfect mix of form and function with the 32" four-blade Drift fan
- Reversible Medium Cherry and Classic Walnut blades
- Rich Architectural Bronze finish
- Features a dual mount system and a three-speed pull chain fan switch
- Indoor ceiling fan ideal for smaller spaces, such as closets, mudrooms and laundry rooms
- Drift features a powerful motor and a steep pitch to circulate a lot of air within a smaller space
- The design features sleek and modern blades and lends itself to Contemporary, Mid-Century Modern and Modern design trends
- Powerful and reversible 3-speed motor with triple-capacitor control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size up to 75 square feet
- Dual ceiling mounting on downrod, or close to ceiling (9-1/2")
- A 1"x 6" downrod is included. Longer accessory downrods can be ordered separately
- Compatible with universal light kits
- UL dry location listed
- Limited Lifetime Warranty
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting bracket for outlet box included
- 80" of wire supplied
- Medium Cherry/Classic Walnut reversible blades, mdf construction
- Chrome pull chain with Walnut fob
- Triple capacitor speed control, manual reverse control Speed, Manual Reverse
- Airflow: 1953 CFM*
- Energy consumption: 24 watts (excluding lights)*
- Airflow efficiency: 81 cfm/watt*
- * Fan on a downrod

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
Warranty	Limited Lifetime
Labels	ULus Dry location listed

P250008-129

Images:



Dimensions:

Diameter: 32"
Height: 14-3/8"
CTC: 9-1/2"