

Description:

Add a cool breeze to your favorite living space with the Vernal Collection 60-Inch 5-Blade Silver LED Wifi Transitional Indoor/Outdoor Smart Ceiling Fan. Enjoy smart living technology by controlling your ceiling fan and light with your smart device or voice control via our Smart by Bond Wifi app. Customize your home oasis by selecting from the fan's 6 speeds, 3 timer selections, light on/off with full-range dimming, and a breeze mode. Fan and app are compatible with Amazon, Alexa, Google Home, and a variety of other smart devices.

Specifications:

- Built-In Wifi: Enjoy smart living technology by controlling your ceiling fan and light with your smart device or voice control via our Smart by Bond Wifi app.
- Smart Technology: Fan and app are compatible with Amazon Alexa, Google Home, and a variety of other smart devices.
- Application: Ideal for any bedroom, living room, great room, or covered porch.
- Style: Perfect for transitional style settings.
- Blades: Five slightly curved ABS blades are coated in a sleek silver finish that will complement a variety of living areas.
- Dimensions: Measures 60-inch width b 14.25-inch height.
- Lighting: For ideal illumination, an integrated dimmable LED module light source is included (18w, 3000K, 90CRI). The light source is covered by a shatterproof white opal shade.
- Room Size: Light experts recommend installing this fan in a room 400-square feet or larger for optimal performance.
- Certifications: cETLus damp location listed, Title 20, Title 24.
- Customer Support: We guarantee your complete satisfaction with your purchase and offer professional after-sales customer service support.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 7 W., 2.5 ht., 7 depth
- 80 in of wire supplied

Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,600/88 (LM-79)
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	cETLus Damp Location Listed Meets California Title 24 JA8-2016

P250059-152-30



Dimensions:

Length: 60 in
 Diameter: 60 in
 Height: 14-1/4 in

Shatterproof White Lens
 Width: 7-3/164 in
 Height: 1-3/83 in

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$6

\$3

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 21 Watts

All estimates based on typical use, excluding lights

Airflow

5,073

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 242 Cubic Feet Per Minute Per Watt

ftc.gov/energy