

# Byars

Ceiling downrod Mounted • Dry Location Listed **PROGRESS LED**

## Description:

Byars 54" 5-Blade Integrated LED Indoor Matte Black Mid-Century Modern Ceiling Fan with Light Kit and White Opal Shade and Remote Control

## Specifications:

- White Opal Polycarbonate Bowl (uplight), White Opal Polycarbonate Bowl (downlight)
- Fan controlled by the included remote control
- Canopy covers a standard 4" recessed outlet box: 5.875 in W., 2.5 in ht., 5.875 in depth
- Hdwr. Included
- 80 in of wire supplied

## Performance:

Input Power	18 W (downlight)
Input Power	13 W (uplight)
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Down-Source)	1400/78
Lumens/LPW (Up-Source)	1100/85
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	cULus Dry Location Listed
	DC motor

# P250061-31M-30



## Dimensions:

Diameter: 54 in  
 Height: 16 in

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

**\$5**

\$3

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day  
 • **Your cost depends on rates and use**  
 • Energy Use: 18 Watts

**Airflow**

**4,527**

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move  
 • Airflow Efficiency: 250 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy