

AirPro

Ceiling downrod Mounted • Dry Location Listed

Description:

AirPro 52-Inch White 5-Blade AC Motor Traditional Ceiling Fan

Specifications:

- Canopy covers a standard 4" recessed outlet box: 5.875 in W., 2.5 in ht., 5.875 in depth
- Mounting Bracket
- 80 in of wire supplied

Performance:

Input Voltage	120 V
Input Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime warranty
Labels	UL Dry Location Listed
	AC motor

P250066-030



Dimensions:

Diameter: 52 in
Height: 13-1/2 in

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$8.35

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 30 Watts

Airflow

3,097

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 104 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy