

## Carrollwood

• Dry Location Only **PROGRESS LED**

### Description:

Carrollwood Collection 56-Inch Reversible Six-Blade American Walnut/Silver DC Motor Contemporary Ceiling Fan

### Specifications:

- White Opal Polycarbonate light cover
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 6 in W., 2.5 in ht., 6 in depth
- Mounting Plate
- 80 in of wire supplied

### Performance:

Number of Modules	1
Input Power	18 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,400
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	UL Dry Location Only Meets California Title 24 JA8-2016 DC motor

# P250074-009-30



### Dimensions:

Diameter: 56 in  
 Height: 18 in

White Opal Polycarbonate light cover  
 Width: 8 in  
 Height: 4-3/4 in

## ENERGYGUIDE

**Estimated  
Yearly Energy Cost**

**\$6**

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 21 Watts

**Airflow**

**4,758**

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move.
- Airflow Efficiency: 224 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

# P250074-009-30

## Dimming Notes:

---

P250074-009-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Eaton AAL06

IDevices IDEV009

Leviton 6681

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.