

Air Pro Fan

Ceiling downrod Mounted • Dry Location Listed **PROGRESS LED**

Description:

Air Pro 52 in. White 5-Blade AC Motor Ceiling Fan with Light


Specifications:

- Etched White Polypropylene Shatter Resistant Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- Hdwr. Included
- 80 in of wire supplied

Performance:

Number of Modules	2
Input Power	9 W
Input Frequency	60 HzCRI 90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	30-year Limited Warranty
Labels	UL Dry Location Listed
	AC motor

P250078-030-WB



Dimensions:

Diameter: 52 in
Height: 16-11/16 in

Etched White Polypropylene Shatter Resistant Diffuser

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$8

\$3

▼

\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
• **Your cost depends on rates and use**
• Energy Use: 30 Watts

Airflow

3,289

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
• Airflow Efficiency: 111 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy