

Air Pro Builder Fan

Ceiling downrod Mounted • Dry Location Listed

Description:

Air Pro 52 in. Polished Chrome 5-Blade AC Motor Transitional Ceiling Fan

Specifications:

- Canopy covers a standard 4" recessed outlet box: 5 in W., 2.25 in ht., 5 in depth
- Hdwr. Included
- 80 in of wire supplied

Performance:

| | |
|-----------------|--------------------------------|
| Input Frequency | 60 Hz |
| EMI/RFI | FCC Title 47, Part 15, Class B |
| Warranty | 30-year Limited Warranty |
| Labels | UL Dry Location Listed |
| | AC motor |

P250080-015



Dimensions:

Length: 52 in
 Diameter: 52 in
 Height: 12-1/2 in



Side A
Black

Side B
Rustic Charcoal

ENERGYGUIDE

**Estimated
Yearly Energy Cost**

\$10

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • **Your cost depends on rates and use**
 • Energy Use: 36 Watts

Airflow

3,328

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 93 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

REVERSIBLE FAN BLADE FINISHES