

FRESNO

Ceiling mounted • Dry location listed



Description:

Five-blade 60" Fresno ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefits. A white opal glass shade features an 18W dimmable, 3000K LED module. Full range dimming and remote control with batteries is included. Featuring reversible blades, the fan has an Antique Bronze finish. Can be used to comply with California Title 20. Can be used to comply with 2016 Title 24 JA8.

Specifications:

- Antique Bronze (-20) (painted)
- Steel construction
- White opal glass bowl
- Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- The light kit contains a frosted glass shade and is comprised of a 18W dimmable 3000K LED module, offering 1400 lumens, 90+ CRI
- A full function remote with batteries is included - and controls full range dimming and fan speed capabilities including reverse
- Oversized ceiling fan ideal for use in spacious areas, such as large great rooms, living rooms, bedrooms and bonus rooms
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Mounting hardware is included
- Can be used to comply with California Title 20.
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- 80" of wire supplied
- Dark Walnut/Cherry reversible blades, plywood construction
- 14 degree blade pitch
- Full Function Remote Included
- Three speed control
- Meets California Title 24 JA8-2016
- Airflow: 5718 CFM*
- Energy consumption: 79 watts (excluding lights)*
- Airflow efficiency: 72 cfm/watt*
- * Fan on a downrod

Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1400/77.8 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	(L70/TM-21)
EMI/RFI	FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
	Meets California Title 24 JA8-2016

P2548-2030K


Images:



Dimensions:

Diameter: 60"

Height: 17-1/4"



P2548-2030K

Dimming Notes:

P2548 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

"Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Lutron - AYCL-153P

Lutron - AYLV-600P

Lutron - MAELV-601

Leviton - AWRMG-EAW"

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.