

VOX

 Ceiling mounted • Dry location listed **PROGRESS LED**

Description:

Five-blade 52" Vox Hugger ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefits. A shatterproof, white opal shade contains a 17W dimmable, 3000K LED module. A remote control with batteries is included. The fan mounts close to the ceiling. Can be used to comply with California Title 20.

Specifications:

- Antique Bronze (-20) (Painted)
- Steel construction
- Etched opal glass Diffuser
- A shatterproof, white opal shade contains a 17W dimmable, 3000K LED module with 90CRI and 1400 lumens
- Indoor ceiling fan ideal for rooms with low ceiling heights
- Features American Walnut blades and an Antique Bronze finish
- Vox hugger fan mounts close to the ceiling only
- A full function hand held remote control with fan speed control, including reverse, and full range light dimming is included and comes with a convenient wall bracket for storage
- Features modern styling for contemporary living spaces
- Reversible motor for year round comfort allows you to choose either a down drafts (summer) or an up draft (winter)
- Remote control may be replaced by a P2631-30 wall control
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that ranges from 226- to 400-square feet
- UL Dry location listed and rated for indoor use
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 4276 cfm, Energy consumption- 62 watts (excluding lights), Airflow efficiency- 68 cfm/watt
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 80" of wire supplied
- American Walnut blades, plywood construction
- 12 degree blade pitch
- Full Function Remote Included
- Meets Colifornia Title 24 - JA8 - 2016

Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW	1386/77 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
EMI/RFI	Title 20
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
	Meets Colifornia Title 24 - JA8 - 2016

P2572-2030K

Images:



Dimensions:

 Diameter: 52"
 Height: 11-5/8"

 Glass
 Width: 9-9/16"
 Height: 2-3/8"

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$11

\$3 | | | \$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- **Your cost depends on rates and use**
- Energy Use: 40 Watts

Airflow

3,040

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 76 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy