

Braden

Ceiling Mounted • Dry Location Listed **PROGRESS LED**

Description:

Braden 56" Integrated LED Indoor Matte Black Mid-Century Modern Ceiling Fan with Light Kit and White Opal Shade and Remote Control

Specifications:

- White Opal Glass Flat Round
- Dimmable to 10% brightness (See Dimming Notes)
- Fixture covers a standard 4" recessed outlet box: 7.75 in W., 7.75 in depth
- Hdwr. Included
- 10 in of wire supplied

Performance:

Input Power	18 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1,400/78 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	Limited Lifetime Warranty
Labels	cULus Dry Location Listed Meets California Title 24 JA8-2016 AC motor

P2588-31M30K



Dimensions:

Diameter: 56 in
 Height: 9-3/4 in

White Opal Glass Flat Round
 Width: 6 in
 Height: 1-1/2 in

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$10

\$3\$34

Cost Range of Similar Models (19" – 84")

- Based on 12 cents per kWh and 6.4 hours use per day
- Your cost depends on rates and use
- Energy Use: 37 Watts

All estimates based on typical use, excluding lights

Airflow

3,118

Cubic Feet Per Minute

- The higher the airflow, the more air the fan will move
- Airflow Efficiency: 85 Cubic Feet Per Minute Per Watt

ftc.gov/energy

P2588-31M30K

Dimming Notes:

P2588-31M30K is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T VTELV-300

Lutron_Diva DVELV-300P

Lutron_Diva DVCL-253P

Lutron_Caseta Wireless

IDevices_IDEV0009

Leviton_SureSlide 6672

Leviton_SureSlide 6674

Lutron_Ariadni AYCL-153P

Lutron_Toggler TGCL-153PH-WH

Lutron_Ariadni AYLV-600P

Lutron_Maestro MAELV-601

Leviton_AWSMT-EAW

Lutron_Nova N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.