

## Air Pro Edgelit LED Light Kit

Ceiling fan light kit Mounted • Dry Location Listed PROGRESS LED



### Description:

AirPro 7" 1-Light Painted Nickel Edgelit Transitional Ceiling Fan Light Kit and Opal Shade

### Specifications:

- White Opal Polystyrene Flat Round
- Hdwr. Included
- 6 in of wire supplied

### Performance:

|                        |                                    |
|------------------------|------------------------------------|
| Input Power            | 14 W                               |
| Input Voltage          | 120 V                              |
| Input Frequency        | 60 Hz                              |
| Lumens/LPW (Delivered) | 940/67 (LM-79)                     |
| CCT                    | 3000 K                             |
| CRI                    | 90 CRI                             |
| Life (hours)           | 50000 (L70/TM-21)                  |
| EMI/RFI                | FCC Title 47, Part 15, Class B     |
| Warranty               | 5-year Limited Warranty            |
| Labels                 | UL Dry Location Listed             |
|                        | ENERGY STAR® qualified             |
|                        | Meets California Title 24 JA8-2016 |

## P260002-152-30



### Dimensions:

Diameter: 7-3/8 in  
Height: 1 in