



**Description:**

Four-light universal fan light kit features etched Light Topaz glass shades beautiful in design. Antique Bronze finish corresponds with an Antique Brass pull-chain and medium oak fob. Universal style for use with fans that accept an accessory light comes with quick-connect wiring. Includes four 3000K, 800 lumen each (source), Title 24 certified LED bulbs.

**Specifications:**

- Tea Stained glass Shade
- Add style and light to your ceiling fan with this universal fan light kit.
- Alabaster style glass shades
- Antique Brass pull chain/ w medium oak fob included.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Includes four 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016.
- Fully dimmable with dimmable bulbs.
- 6 in of wire supplied

**Performance:**

Number of Lamps	4
Input Power	9 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	800/88 (LM-82)
CCT	3000 K
CRI	90 CRI
Life (hours)	25000 (L70/TM-21)
EMI/RFI	Title 24
Max. Operating Temp	40 °C
Warranty	1-year Limited Warranty
Labels	UL Dry Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016


**P2643-20TWB**



**Dimensions:**

Diameter: 13-3/4 in  
 Height: 8 in

Tea Stained glass Shade  
 Width: 5-3/8 in  
 Height: 4-7/8 in





# P2643-20TWB

## Dimming Notes:

---

P2643-20TWB is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron\_Diva DVELV-300P

Lutron\_Nova T NTELV-300

Lutron\_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.