

**AirPro** Universal -use with any indoor fan with 1/8" IPS light kit adapter • Dry Location Listed



**Description:**

Four-light universal fan light kit features alabaster style glass shades beautiful in design. White finish corresponds with a Chrome pull-chain and white fob. Universal style for use with fans that accept an accessory light comes with quick-connect wiring. Includes four 3000K, 800 lumen each (source), Title 24 certified LED bulbs.

**Specifications:**

- Alabaster glass Shade
- Add style and light to your ceiling fan with this universal fan light kit.
- Alabaster style glass shades
- Chrome pull chain w/ white fob included.
- Quick-connect wiring to any progress fan that accept an accessory light.
- Includes four 3000K, 800 lumen each (source), Title 24 certified LED bulbs
- Energy Star Qualified
- Meets California T24 JA8-2016.
- Fully dimmable with dimmable bulbs.
- 6 in of wire supplied

**Performance:**

|                     |                                    |
|---------------------|------------------------------------|
| Number of Lamps     | 4                                  |
| Input Power         | 9 W                                |
| Input Voltage       | 120 V                              |
| Input Frequency     | 60 Hz                              |
| Lumens/LPW (Source) | 800/88 (LM-82)                     |
| CCT                 | 3000 K                             |
| CRI                 | 90 CRI                             |
| Life (hours)        | 25000 (L70/TM-21)                  |
| EMI/RFI             | Title 24                           |
| Max. Operating Temp | 40 °C                              |
| Warranty            | 1-year Limited Warranty            |
| Labels              | UL Dry Location Listed             |
|                     | ENERGY STAR® qualified             |
|                     | Meets California Title 24 JA8-2016 |


**P2643-30WB**



**Dimensions:**

Diameter: 13-3/4 in  
Height: 8 in

Alabaster glass Shade  
Width: 5-3/8 in  
Height: 4-7/8 in



13-5/8"

**Dimming Notes:**

---

P2643-30WB is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

**Dimming Controls:**

---

Lutron\_Diva DVELV-300P

Lutron\_Nova T NTELV-300

Lutron\_Maestro MAELV-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

# P2643-30WB