

Linear Vanity

Wall mounted • Dry location listed

Description:

Modern architectural styling frames with an integrated LED source and circular etched opal glass. For increased design options, fixtures can be installed horizontally or vertically. Frame 12" bath and vanity fixture provides beautiful and continuous illumination, as well as energy saving benefits. 3000K, 90+ CRI. Complimented by a Architectural Bronze finish.

Specifications:

- Architectural Bronze (-129) (painted)
- Steel Construction
- Etched White glass diffuser
- Modern architectural styling.
- Integrated LED source and circular etched opal glass.
- Fixtures can be installed horizontally or vertically.
- Dimmable to 10% with many ELV dimmers
- 577 lumens 36 lumens/watt (delivered)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting bracket for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA

Performance:

Number of Modules	1
Input Power	15w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	577/36.1 (LM-79)
CCT	3000 K
CRI	93
Life (hours)	42,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	ETL Dry location listed

P2781-12930K9

Images:



Dimensions:

Width: 12"
 Depth: 3-7/16"
 Height: 4-3/4"
 H/CTR: 2-3/8" (mounted horizontal)

LED lighting facts [®]	
A Program of the U.S. DOE	
Light Output (Lumens)	626
Watts	16.2
Lumens per Watt (Efficacy)	38.64
Color Accuracy Color Rendering Index (CRI)	90
Light Color Correlated Color Temperature (CCT)	3000 (Bright White)
<small>All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.</small>	
<small>Visit www.lightingfacts.com for the Label Reference Guide.</small>	
<small>Registration Number: TH84-OSTGM3 (5/4/2016)</small>	
<small>Model Number: P2781-12930K9</small>	
<small>Type: Luminaire - Decorative</small>	

P2781-12930K9**Dimming Notes:**

P2781 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron Diva DVELV-300P

Lutron Nova T NTELV-300

Lutron Diva DVELV-300P

Lutron Caseta

Lutron Ariadni AY-600P

Leviton Illumatech IPI06-1LZ

Lutron Lumea LG-603PG

Leviton SureSlide 6672

Leviton SureSlide 6674

Lutron Ariadni AYCL-153P

Lutron Skylark Contour CTCL-153P

Lutron Diva DVCL-153P

Pass & Seymour Harmony DCL453PTCCCV6

Lutron Toggler TGCL-153P

Lutron Maestro MACL-153M

Lutron Ariadni AYL-600P

Lutron Maestro MA-600

Lutron NOVA T NTLV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Lutron Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.