

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P2784-77

Kensington

The casual, comfortable feel of the Kensington Collection is perfect for many interiors. Two-light bath bracket features skillfully scrolled metalwork in a Forged Bronze finish. Trumpet-shaped, slightly textured glass shades are complemented by a frosted caramel swirl finish. These rich details come together to create a rich focal point for any room and offers a charming appeal for any interior.

Category: Bath & Vanity

Finish: Forged Bronze (painted)

Construction: Steel construction

Glass: Frosted caramel swirl glass trumpet shaped shades



Width: 15"
Height: 9-1/2"
Depth: 7-5/8"
H/CTR: 6-3/8"

Glass: 6" dia.
 Height: 5"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Mounts in "up" or "down" position Back plate covers a standard 4" hexagonal recessed outlet box 9" W., 5"	Threaded socket ring secures glass Pre-wired 6" of wire supplied 120V	Quantity: 2 100W Medium Base Medium ceramic sockets	UL-CUL Damp location listed 1 year warranty Companion Bath and Vanity, Ceiling Fans, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available