

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P2879-77

Fiorentino

Three-light foyer with clear seeded glass and champagne drip glass candles. Hand-painted Forged Bronze finish blends brown and black tones, and faint golden highlights. Combines etched detailed columns and banding to stylized leaves.

Category: Hall & Foyer

Finish: Forged Bronze (painted)

Construction: Steel construction, Aluminum

Clear seeded glass bowl



Diameter: 15-7/8"
Height: 35-7/8"
Overall ht. w/chain: 111"

Glass: 14" dia.

Height: 15"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling chain mount Mounting strap for outlet box included Six feet 9 gauge chain supplied Canopy covers a standard 4" hexagonal recessed outlet box	Pre-wired Fifteen feet of wire supplied 120V	Quantity: 3 60W Candelabra Base Candelabra phenolic sockets	UL-CUL Dry location listed 1 year warranty Companion Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available