

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_



Incandescent

# P300148-015-WB

## Circuit

Connectivity and electric circuit diagrams inspired the design behind this new bath and vanity collection. Circuit fixtures appear to contain a lamp that is a continuous tube for an intriguing appearance. This collection is ideal for residential or light commercial applications, such as restaurants or other urban industrial and vintage electric design schemes. One-Light Bath in a Polished Chrome finish.

**Width: 13-1/2"**  
**Height: 5-1/8"**  
**Depth: 3"**  
**H/CTR: 2-1/2"**

- This collection is ideal for residential or light commercial applications, such as restaurants or other urban industrial and vintage electric design schemes
- Ideal for modern farmhouse, rustic farmhouse and urban industrial design styles
- Features popular Polished Chrome finish
- Design inspired by electric diagrams creating the feeling of a completed circuit
- Uses one 40-watt medium base bulb. One 40w T10 vintage bulb included with fixture. Replacement T10 vintage bulbs are P860028-001.
- Circuit fixtures appear to contain a lamp that is a continuous tube for an intriguing appearance
- Adds task lighting on either side - or above - of mirror to eliminate shadows on face when getting ready in the morning
- In addition to bath areas, sconces are suitable for hall & foyers to add ambient lighting.

**Category:** Bath & Vanity

**Finish:** Polished Chrome (plated)

**Construction:** Steel Construction

| MOUNTING  | ELECTRICAL                       | LAMPING   | ADDITIONAL INFORMATION                                     |
|---|----------------------------------|---|--|
| Wall mounted<br><br>Mounting strap for outlet box included<br><br>Fixture can be installed with glass facing up or down<br><br>Back plate covers a standard 4" octagonal recessed outlet box<br><br>Back plate: 5.125" W., 5.125" ht., 0.875" depth | 6" of wire supplied<br><br>120 V | Quantity:<br><br>One 40w max. Medium Base (T10) or LED equivalent(included)<br><br>E26 base | cCSAus Damp location listed<br><br>1-year Limited Warranty |