

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

P300175-015

Signal

A clean, classic duo of clear, blown glass shades encapsulate exposed bulbs affixed to round, Polished Nickel bases. A smooth, sleek bar supports the light fixtures and anchors them to a shiny, circular backplate. This set of classic twins are perfect for illuminating a hallway, bathroom or dressing table mirror, or wherever essential task light is needed in coastal, modern farmhouse and modern interior settings.

- Perfect for installing above a bathroom or dressing table mirror, in a hallway, or wherever focused task light is desired
- Two-light bath vanity with simple, clean lines
- Offers a clean, minimalist approach ideal for coastal, modern farmhouse, and modern interiors
- Round backplate holds a single bar supporting the light fixture surrounded by a clear, blown glass shade
- Finished in Polished Chrome
- Can be mounted facing up or down
- Measures 13-1/2 in width X 9-1/8 in height, extends 5-3/8 in, H/CTR 2-5/8 in
- Includes installation instructions and mounting hardware
- Uses two 60-watt max medium base bulbs, or the LED equivalents, that are sold separately
- Progress Lighting products are designed for exceptional quality, reliability, and functionality



Width: 13-1/2"
Height: 9-1/8"
Depth: 5-3/8"
H/CTR: 2-5/8" (glass facing up)

Glass
 Width: 3-1/2"
 Length: 3-1/2"
 Height: 6-1/2"

Category: Bath & Vanity

Finish: Polished Chrome (Plated)

Construction: Steel Construction

Glass/Shade: Clear Glass Cylindrical

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting Strap for outlet box included Fixture can be installed with glass facing up or down Canopy covers a standard 4" octagonal recessed outlet box 5.125" W., 1" ht., 5.125" depth	Pre-wired 6" of wire supplied 120 V	Quantity: Two 60w max. Medium Base E26 base Porcelain sockets	cULus Damp location listed 1 year warranty