

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

## P300190-009 Axle

Axle Collection 2-Light Brushed Nickel Vintage Wall Light

**Category:** Bath & Vanity  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction



Length: 16 in  
Extends: 7 in  
Height: 6-3/4 in  
H/CTR: 3.69 in (facing up)

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 60 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty

Fixture can be installed with glass facing up or down

Canopy covers a standard 4" recessed outlet box: 6.125" W., 0.875" ht., 6.125" depth