

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P300226-009

## Rushton

Decorate and add functional lighting to either side of a mirror or throughout the home with the timeless Rushton one-light bath. A single exposed bulb surrounded by a clear glass shade hangs from an antique-style socket. The faux cord extending from the Brushed Nickel backplate wraps around the miniature pulley wheel to create a one-of-a-kind arm to hold the fixture in place. With its tasteful industrial design, this piece is ideal as a bath vanity or wall sconce in industrial and farmhouse settings.

- Perfect as a bath vanity on either side of a mirror or as a wall sconce throughout the home wherever a vintage touch is desired
- Antique styling is ideal for industrial and farmhouse settings
- One-light bath vanity offers a vintage charm that preserves a sense of history
- Industrial pulley wheel detailing with faux metal cord is offset by a simple rectangular backplate
- Mixed-metal finish of Brushed Nickel accented with a Black tube arm
- Measures 5 in width X 9-1/2 in height, Extends 6 in, H/CTR 6-1/2 in
- Uses one 60-watt max medium base bulb, or LED equivalent, that is sold separately
- Includes installation instructions and mounting hardware
- Progress Lighting products are designed for exceptional quality, reliability, and functionality

**Category:** Bath & Vanity

**Finish:** Brushed Nickel (Plated)

**Construction:** Steel Construction

**Glass/Shade:** Clear Glass Bell



**Width:** 5"  
**Height:** 9-1/2"  
**Depth:** 6"  
**H/CTR:** 6-1/2" (glass facing up)

**Width:** 4-1/2"  
**Length:** 4-1/2"  
**Height:** 5-1/4"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted  Mounting plate for outlet box included  Fixture can be installed with glass facing up or down  Canopy covers a standard 4" octagonal recessed outlet box  5" W., 6" ht., 0.75" depth	Pre-wired  6" of wire supplied  120 V	Quantity:  One 60w max. Medium Base  E26 base Porcelain socket	cULus Damp location listed  1 year warranty