

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300321-163 Aiken

Aiken Collection 2-Light Vintage Brass Clear Glass Vintage Bath Vanity Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylinder



Length: 14-5/8 in
Extends: 7 in
Height: 9-7/8 in
H/CTR: 4-3/16 in (glass facing up)

Clear Glass Cylinder
Width: 4-3/16 in
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 60 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty

Fixture can be installed with glass facing up or down

Canopy covers a standard 4" recessed outlet box: 7.125" W., 4.5" ht., 0.75" depth