

## Grid LED

Wall Mounted • Damp Location Listed **PROGRESS LED**

### Description:

Grid LED Collection 22-inch Black and White Linen Acrylic Modern Style Bath Vanity Wall Light


### Specifications:

- White Linen Acrylic Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 8.25 in W., 4.75 in ht., 1.125 in depth
- Mounting backplate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

### Performance:

Number of Modules	1
Input Power	22 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,033/46 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed Meets California Title 24 JA8-2019


# P300332-031-30



### Dimensions:

Width: 22 in  
 Extends: 3-1/8 in  
 Height: 4-3/4 in  
 H/CTR: 2-3/8 in (mounted horizontal)

White Linen Acrylic Shade  
 Length: 22 in  
 Width: 1-11/16 in  
 Height: 3-11/16 in



# P300332-031-30

## Dimming Notes:

---

P300332-031-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Lutron NTEVL-300

Lutron DVELV-300P

Lutron Caseta Wireless

Lutron AYCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.