

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300397-31M
Singleton

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Bowl

Width: 26-1/2 in
Extends: 9 in
Height: 8 in
H/CTR: 5-5/8 in (glass facing up)

Clear Glass Bowl
Width: 7-5/8 in
Height: 4-5/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Back Plate covers a standard 4" recessed outlet box: 8" W., 4.43" ht., 0.87" depth		Fully dimmable with dimmable bulbs	