

## Three-Light Close-To-Ceiling

Wall or ceiling mounted • Damp location listed



### Description:

Transit is a uniquely styled series with clean design flexibility. This three-light LED close to ceiling featuring a white acrylic diffuser and Antique Bronze finish can mount to either ceiling or wall.

### Specifications:

- Antique Bronze (-20) (painted)
- Steel Construction
- White acrylic diffuser
- Replaceable LED module.
- 1,211 lumens 71.2 lumens/watt per module (source)
- 3000K color temperature, 90+ CRI.
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA
- ENERGY STAR® qualified

### Performance:

Number of Modules	3
Input Power	17w per module
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1211/71.2 (LM-82) per module
Lumens/LPW (Delivered)	1874/36.9 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cCSAus Damp location listed ENERGY STAR® qualified

## P3432-2030K9

### Images:



### Dimensions:

Square: 18"  
Depth: 3-3/4"  
Height: 3-3/4"  
H/CTR: 9"

## P3432-2030K9

### Dimming Notes:

---

P3432 is designed to be compatible with many ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

### Dimming Controls

---

Lutron Nova T NTELV-300

Lutron Verti VTELV-600

Lutron Maestro MAELV-600

Lutron spacer/system SPSELV-600

Leviton Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.