

ONE-LIGHT FLUSH MOUNT

Ceiling mounted • Damp location listed **PROGRESS LED**

P350055-009-30

Description:

A 12" domed, linen finish glass diffuser is discreetly supported from Brushed Nickel metal fittings and encloses an LED light source. 1,000 lumens 90+ CRI, 3000K.

Specifications:

- Brushed Nickel (-009) (plated)
- Steel Construction
- Etched White Linen glass diffuser
- Design features a domed, linen finish glass diffuser.
- Diffuser is discreetly supported from metal fittings encloses an energy-efficient light source
- 1600 source lumens 80 lumens/watt (source)
- 3000K color temperature, 90+ CRI.
- This fixture is not dimmable.
- Fixture covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included

Performance:

Number of Modules	1
Input Power	20w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1600/80 (LM-82)
Lumens/LPW (Delivered)	1000/50 (LM-79)
CCT	3000 K
CRI	90+
Life (hours)	(L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-30 °C
Max. Operating Temp	30 °C
Warranty	5 year warranty
Labels	cETLus Damp location listed

Images:



Dimensions:

Diameter: 12"
Height: 4-1/4"

Glass
Width: 11-3/4"
Height: 3"