

Maier LED

Wall or Ceiling Mounted • Damp Location Listed **PROGRESS LED**

Description:

Maier Collection 9" LED Flush Mount

Specifications:

- White Acrylic Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Unit covers a standard 4" recessed outlet box: 8.875 in W., 1.3125 in ht., 8.875 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	23 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,600/69.6 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	36000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	ETL Damp Location Listed
	Meets California Title 24 JA8-2016

P350076-030-30



Dimensions:

Diameter: 9-1/16 in
 Height: 4-5/16 in



P350076-030-30

Dimming Notes:

P350076-030-30 is designed to be compatible with many Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Nova T VTELV-300

Lutron_Diva DVELV-300P

Lutron_Diva DVCL-253P

Lutron_Caseta Wireless

Lutron_Ariadni AYLV-600P

Lutron_NTLV-600

Lutron_Maestro MAELV-601

Lutron_Nova N-600

Leviton_Trimatron 6681

Leviton_SureSlide 6672

Leviton_SureSlide 6674

Leviton_Renoir II AWRMG-EAW

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.