

LED Flush Mount

 Flush-Mount Mounted • Damp Location Listed **PROGRESS LED**

Description:

One-Light 11" LED Flush Mount

Specifications:

- Etched Glass Globe
- Dimmable to 10% brightness (See Dimming Notes)
- Ceiling pan covers a standard 4" recessed outlet box: 11 in W., 1.25 in ht., 11 in depth
- Mounting strap for outlet box included
- 6 in of wire supplied

Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,202/67 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	Meets FCC Title 47, Part 15 Class B
Max. Operating Temp	30°C
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2016

P350100-020-30



Dimensions:

Diameter: 11 in
Height: 4-1/4 in

Etched Glass Globe
Width: 10 in
Height: 3-1/4 in



P350100-020-30

Dimming Notes:

P350100-020-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_Diva DVELV-300P

Leviton_SureSlide 6674

Lutron_Diva DVCL-153P

Legrand_RHCL453

Eaton_SUL06P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.