

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P350129-012 Inspire

Inspire Collection Two-Light Satin Brass Summer Linen Shade New Traditional Semi-Flush Light

Category: Close-to-Ceiling

Finish: Satin Brass (Plated)

Construction: Steel Construction

Glass/Shade: Summer Linen Fabric Shade, Etched Glass Diffuser



Diameter: 13 in
Height: 10-1/8 in

Summer Linen Fabric Shade

Width: 13 in
Height: 4-1/2 in

Etched Glass Diffuser

Width: 12-5/8 in
Height: 0-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling semi-flush	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 5.1875" W, 1.4375" ht., 5.1875" depth		Incandescent: 75-watt MAX per socket LED: 15-watt MAX per socket	
		Fully dimmable with dimmable bulbs	